

Enclosure Heaters

Cabinet Enclosure Heaters

Tempco enclosure heaters are the answer to all your enclosure heater needs. Our heaters are designed to help electric, electronic, pneumatic, hydraulic and mechanical equipment perform at top capacity by protecting them against low temperatures, condensation and corrosion. Tempco offers many different styles of heaters that can be used in enclosure heating applications. Our most popular styles are displayed on the next few pages.

Tubular Heater
See Page 11-115

Silicone Rubber Heater
See Page 9-18

Patent
Pending

Ceramic Heater
See Page 7-41

Finned Strip Heater
See Page 8-15

Typical Applications

- ✦ Traffic Signal Control Boxes
- ✦ Automatic Teller Machines
- ✦ Outdoor Electrical Power Enclosures
- ✦ Control Panels
- ✦ Control Valve Housings
- ✦ Switch Gear
- ✦ Clothing Lockers

Determining the Minimum Wattage for Your Application

1. Determine the lowest temperature to which the enclosure is expected to be exposed.
2. Determine the operating temperature to which you want the enclosure heated.
3. Subtract the ambient temperature from the enclosure temperature to get the temperature change required.
4. Calculate the surface area of the enclosure. For a rectangular enclosure use the formula:

$$2 [(Length \times Width) + (Length \times Height) + (Width \times Height)]$$
5. Select the correct table below depending upon whether your box is insulated or non-insulated. Read from the table the wattage required depending upon your calculated temperature change and surface area.
6. Add an additional 50% of the determined wattage if the enclosure is to be located in windy conditions.

Selecting the Right Heater for Your Application

1. Determine the wattage of heater(s) that you need. See the instructions on this page to determine your wattage requirements.
2. Determine the type of heater that you need. Depending upon conditions, one heater type might be better than others. Items to take into consideration are space constraints inside the enclosure and wattages required.
3. Determine the number of heaters you need. You can combine multiple heaters to achieve your wattage requirements.
4. Determine how you will control the heaters. Will you use built-in thermostats to monitor the temperature? Or will you use a single temperature control to monitor and control the heaters? Tempco manufactures a wide range of temperature control devices and when multiple heaters are required, Tempco can supply you with the temperature controls that will meet your needs.

Insulated Enclosure Wattage Selection Table


Δ Temperature		TOTAL SURFACE AREA ft² (m²)													
°F (°C)	2 (0.19)	3 (0.28)	4 (0.37)	5 (0.47)	6 (0.56)	7.5 (0.70)	9 (0.84)	10 (0.93)	15 (1.40)	20 (1.86)	25 (2.33)	30 (2.79)	40 (3.72)	50 (4.65)	
20 (11)	10	10	15	20	20	25	30	35	50	65	80	100	130	160	
40 (22)	15	20	30	35	40	50	60	65	100	130	160	195	260	320	
60 (33)	20	30	45	50	60	75	90	100	145	195	240	290	385	480	
80 (44)	30	40	55	65	80	100	115	130	195	260	320	320	515	640	
100 (56)	35	50	65	80	100	125	145	160	240	320	400	400	640	800	
120 (67)	40	60	80	100	115	150	175	195	290	385	480	480	770	960	
140 (78)	45	70	90	115	135	175	205	225	340	450	560	560	900	1120	

Uninsulated Enclosure Wattage Selection Table

Δ Temperature		TOTAL SURFACE AREA ft² (m²)													
°F (°C)	2 (0.19)	3 (0.28)	4 (0.37)	5 (0.47)	6 (0.56)	7.5 (0.70)	9 (0.84)	10 (0.93)	15 (1.40)	20 (1.86)	25 (2.33)	30 (2.79)	40 (3.72)	50 (4.65)	
20 (11)	30	40	55	70	80	100	120	135	205	270	335	405	540	670	
40 (22)	55	80	110	135	160	200	245	270	405	540	670	805	1075	1340	
60 (33)	90	120	160	205	245	300	365	405	605	805	1005	1210	1610	2010	
80 (44)	110	160	215	270	325	400	485	540	805	1075	1340	1610	2145	2680	
100 (56)	135	200	270	335	405	500	605	670	1005	1340	1675	2010	2680	3350	
120 (67)	165	240	320	405	485	600	725	805	1210	1610	2010	2415	3220	4020	
140 (78)	190	280	375	470	565	700	845	940	1410	1880	2345	2815	3775	4690	

EHT Tubular Enclosure Heaters — Type 1 Box Style


Stock Heaters



Wattage	3-1/2" Square by 8" Long Enclosure		3" Square by 15" Long Enclosure	
	120V	240V	120V	240V
100	EHT00006	—	EHT00017	—
250	EHT00008	EHT00009	EHT00019	EHT00020
350	EHT00010	EHT00011	EHT00021	EHT00022
375	EHT00012	EHT00013	EHT00023	EHT00024
400	EHT00054	EHT00055	EHT00056	EHT00057


Design Features

- * Incoloy tubular heating element
- * Up to 15 w/in²
- * 10-32 terminals standard



EHT Tubular Enclosure Heaters — Type 2 Open Style

Stock Heaters




Wattage	Enclosure Heater			
	No Thermostat		With 30-150°F Thermostat	
	120V	240V	120V	240
100	EHT00029	—	EHT00030	—
150	EHT00031	—	EHT00032	—
250	EHT00033	EHT00046	EHT00034	EHT00047
350	EHT00035	EHT00048	EHT00036	EHT00049
400	EHT00052	EHT00050	EHT00053	EHT00051

Thermostat models include 36" HPN line cord

Design Features

- * Incoloy[®] tubular heating element
- * Available with 30-150°F thermostat prewired with 36" HPN line cord



Ordering Information

Catalog Heaters

Select a **Tubular Enclosure Heater** from the Standard Sizes and Ratings list above.

Custom Engineered/Manufactured Heaters

Standard lead time is 3 weeks. Please Specify the following:

- ☐ **Size:** Provide the length and width of the perforated box desired.
- ☐ **Wattage:** Tubular heater wattages up to 15 w/in²
- ☐ **Termination:** Various terminations are available. Consult Tempco.
- ☐ **Voltage:** All standard

⚠ WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov.

EHA — Remote Thermostats for Enclosure Heaters

Stock EHA Remote Thermostats



See Page 9-18 for details


Opens °F	Closes °F	Part Number
60±5	40±7	EHA00001
140±5	110±10	EHA00002
180±5	150±10	EHA00003

Flexible Heaters

Enclosure Heaters



EHR — Silicone Rubber Enclosure Heater



Mounting slots are 1/4" x 5/32" centered in 1/2" flange.

Standard (Non-Stock) Silicone Rubber Enclosure Heaters

Width	Length	Mounting Center	Watts	Volts	Lead Length	Thermostat (°F)		Part Number
						Opens	Closes	
2½"	5"	3"	25	120	48"	—	—	EHR00001
2½"	5"	3"	25	120	48"	60	40	EHR00002
2½"	5"	3"	35	120	48"	—	—	EHR00003
2½"	5"	3"	50	24	48"	—	—	EHR00039
2½"	5"	3"	50	120	48"	—	—	EHR00004
2½"	5"	3"	50	120	48"	60	40	EHR00005
2½"	6"	4"	60	120	48"	—	—	EHR00006
2½"	6"	4"	60	120	48"	60	40	EHR00007
2½"	6"	4"	60	120	48"	140	110	EHR00008
2½"	6"	4"	60	120	48"	180	150	EHR00009
2½"	10"	7"	70	120	48"	—	—	EHR00010
2½"	10"	7"	100	12	48"	—	—	EHR00049
2½"	10"	7"	100	120	48"	—	—	EHR00011
2½"	10"	7"	100	120	48"	60	40	EHR00012
2½"	10"	7"	100	230	48"	60	40	EHR00028
2½"	12"	9"	80	240	48"	60	40	EHR00032
2½"	12"	9"	120	120	48"	—	—	EHR00013
2½"	12"	9"	120	120	48"	60	40	EHR00014
2½"	12"	9"	120	120	48"	140	110	EHR00015
2½"	12"	9"	120	120	48"	180	150	EHR00016
2½"	12"	9"	120	240	48"	60	40	EHR00034
4½"	10"	7"	140	120	48"	—	—	EHR00017
4½"	10"	7"	250	120	48"	—	—	EHR00018
4½"	10"	7"	250	120	48"	60	40	EHR00019
4½"	10"	7"	250	240	48"	140	110	EHR00044

Design Features

- * Available with or without an Integrated Thermostat (See EHA below for Remote Thermostats)
- * Custom Design and Alternate Thermostat Settings Available
- * Heater Vulcanized to an Aluminum Mounting Plate for Easy Installation
- * 120V Standard; Custom Voltages Available upon Request
- * 48" Teflon® Leads Standard
- * Dimensions Listed are for Heater and Bracket; Actual Heater Width is 1/2" Less
- * Safe to Operate, No Exposed Electrical Connections


EHR — Silicone Rubber Heaters are designed for easy installation and safe operation. These rectangular shaped wire-wound Silicone Rubber Heaters are vulcanized to an aluminum mounting plate with mounting holes. They provide superior protection for enclosures of all types against condensation, humidity and freezing.

It is recommended that the enclosure heater be used with a thermostat either built in or mounted remotely to limit the maximum temperature reached and conserve energy. The suggested mounting method is at the bottom of the enclosure, mounted vertically. If a remote mounted thermostat is preferred, mount the heater on the bottom of the enclosure and the thermostat in the middle of the enclosure.

EHA — Remote Thermostats for Enclosure Heaters

Design Features

- * Standard 16ga Teflon® lead length: 48"
- * Can easily be located anywhere in the enclosure using the pressure sensitive adhesive.
- * Any standard thermostat can be used (see page 13-82 for available ranges)
- * Silicone rubber base and enclosure
- * Ratings: 10A/250 Vac, 15A/120 Vac



EHA00005 D-ring and strap mounting thermostat. Can be applied to sense the air around an object or an object directly.



Ordering Information

Select a **Remote Thermostat** from the list at right.

Custom Engineered/Manufactured Remote Thermostats

Standard lead time is 3 weeks. Please Specify the following:


- ☐ **Range:** Select from the list of thermostats on page 13-82
- ☐ **Lead Length:** Specify any special lead length you require.

Stock EHA Remote Thermostats

Opens °F	Closes °F	Part Number	
		PSA	D-ring & Strap
60±5	40±7	EHA00001	EHA00005
140±5	110±10	EHA00002	—
180±5	150±10	EHA00003	—

WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov.

Standard (Non-Stock) and Stock Sizes and Ratings



Stock Items Are Shown In **RED**


Length in mm	Wattage	Watt Density W/in ² W/cm ²	Part Number	
			120V	240V
8½ 215.9	250	18 3	CSF00252	CSF00039
10½ 266.7	350	17 3		CSF00130
10½ 266.7	500	24 4	CSF00129	
10½ 266.7	600	33 5	CSF00042	
10½ 266.7	725	40 6	CSF00044	CSF00045
10½ 266.7	850	47 7	CSF00209	
12 304.8	500	19 3	CSF00047	
12 304.8	900	34 5	CSF00053	CSF00054
14 355.6	750	23 3	CSF00056	CSF00057
14 355.6	1100	36 6	CSF00060	CSF00061
15¼ 387.4	1000	27 4	CSF00065	
15¼ 387.4	1250	33 5	CSF00143	CSF00067
17⅞ 454.0	1000	23 3	CSF00071	
17⅞ 454.0	1300	28 4	CSF00073	
17⅞ 454.0	1550	30 5	CSF00148	CSF00075
19½ 495.3	1250	24 4		CSF00077

Finned Strip Heaters with T4 Terminals

Stock Items Are Shown In **RED**

Length in mm	Wattage	Watt Density W/in ² W/cm ²	Part Number	
			120V	240V
19½ 495.3	1700	32 5	—	CSF00080
21 533.4	1900	33 5	CSF00158	CSF00085
23¼ 603.3	1000	15 2	—	CSF00528
23¼ 603.3	1450	22 3	—	CSF00088
23¼ 603.3	2200	33 5	—	CSF00090
25½ 647.7	2400	33 5	—	CSF00094
26½ 679.5	2500	32 5	—	CSF00100
30½ 774.7	1800	20 3	—	CSF00102
30½ 774.7	2800	28 4	—	CSF00104
33½ 850.9	3150	31 5	—	CSF00180
35½ 911.2	2000	18 3	—	CSF00350
35½ 911.2	3450	31 5	—	CSF00110
42½ 1079.5	4150	31 5	—	CSF00117

NOTE: Type C – Terminal Box and Type P – High Temperature Quick Disconnect Plug are available. See page 8-6 for details.



EHF — Finned Channel Strip Enclosure Heaters


Design Features

- * 10-32 offset screw terminals (T4 style) standard, other terminations available
- * UL recognized component
- * Stainless steel sheath and fins
- * Easy installation with special enclosure mounting brackets

Stock and Standard (Non-Stock) Series EHF Heaters

Stock Items Are Shown In **RED**

Overall Length	Mounting Dimension	Watts	Part Number	
			120V	240V
12.125	11.375	200	EHF00001	EHF00002
15.625	14.875	350	EHF00003	EHF00004
19.5	18.75	450	EHF00005	EHF00006
25.375	24.625	700	EHF00007	EHF00008



NOTE: See page 7-41, 9-18 and 11-114 for other type enclosure heaters.

Ordering Information

Catalog Heaters

Select a Finned Strip Heater from the Standard Sizes and Ratings lists on pages 8-14 and 8-15.

Finned Strip Heaters whose Part Numbers are in **RED** are available from Stock for immediate delivery.

Standard Non-Stock Part Numbers have a 3-week lead time.

Custom Engineered/Manufactured Heaters

An electric heater can be very application specific; for sizes and ratings not listed, **TEMPCO** will design and manufacture a Finned Strip Heater to meet your requirements. **Standard lead time is 3 weeks.**


Please Specify the following:

- | | |
|--|---|
| ☐ Type of Application | ☐ Termination Type |
| ☐ Length | ☐ Secondary Bushings (see page 8-13) |
| ☐ Wattage | ☐ Igloo™ Ceramic Terminal Covers |
| ☐ Voltage | |

WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov.

(800) 323-6859 • Email: sales@tempco.com

EHC Ceramic E-Mitter Enclosure Heaters



Typical Applications

- ➔ Traffic Signal Control Boxes
- ➔ Automatic Teller Machines (ATMs)
- ➔ Outdoor Electrical Power Enclosures
- ➔ Control Panels
- ➔ Control Valve Housings
- ➔ Switch Gear
- ➔ Clothing Lockers

Tempco enclosure heaters are the answer to all your enclosure heater needs. Our heaters are designed to help electric, electronic, pneumatic, hydraulic and mechanical equipment perform at top capacity by protecting them against low temperatures, condensation and corrosion. Tempco offers many different styles of heaters that can be used in enclosure heating applications. Our most popular styles are displayed below.

EHC Enclosure Heaters with NEMA 1 Housing

Watts	Volts	Color	Part Number	Replacement Heater Bulb
50	120	Rose to Grey	EHC10100	CRT10100
75	120	Rose to Grey	EHC10101	CRT10101
75	240	Rose to Grey	EHC10106	CRT10106
100	120	Rose to Grey	EHC10102	CRT10102
100	240	Rose to Grey	EHC10107	CRT10107
150	120	Rose to Grey	EHC10103	CRT10103
150	240	Rose to Grey	EHC10108	CRT10108
200	120	Rose to Grey	EHC10104	CRT10104
200	240	Rose to Grey	EHC10109	CRT10109
250	120	Rose to Grey	EHC10105	CRT10105
250	240	Rose to Grey	EHC10110	CRT10110

See page 11-114 for help in sizing and determining the best enclosure heater for your application.

EHA — Remote Thermostats for Enclosure Heaters




See Page 9-18 for details

Stock EHA Remote Thermostats

Opens °F	Closes °F	Part Number
60±5	40±7	EHA00001
140±5	110±10	EHA00002
180±5	150±10	EHA00003


Other Types of Enclosure Heaters



Finned Strip Heater
See Page 8-14



Silicone Rubber Heater
See Page 9-18



Tubular Heater
See Page 11-115